

STANDARD HEIGHT CLAMP-ON

Technical drawings of the Standard Height Clamp-On device, showing dimensions in millimeters (mm).

Front View Dimensions:

- Total height: 476mm
- Upper section diameter: $\phi 97\text{mm}$
- Lower section diameter: $\phi 64\text{mm}$
- Clamp-on height: 139mm
- Clamp-on width: 134mm

Top View Dimensions:

- Device width: 134mm
- Device height: 210mm

Side View Dimensions:

- Device width: 85mm
- Device height: 133mm
- Clamp-on height: 368mm
- Clamp-on width: 467mm OR 372mm
- Clamp-on thickness: 40.5mm
- 75mm MAX BAR THICKNESS

LOW OLYMPUS CLAMP-ON

363mm

50mm CLAMP

Ø 64mm

134mm

210mm

85mm

358mm or 263mm

75mm MAX BAR THICKNESS

STANDARD HEIGHT THROUGH BAR

MICRO MATIC

OLYMPUS

INFORMATION SHEET

120mm

194mm

85mm

476mm

368mm

Ø 64mm

Ø 50mm

CLEARANCE HOLE
REQUIRED Ø

75mm MAX BAR
THICKNESS

LOW OLYMPUS THROUGH BAR

363mm

125mm

200mm

85mm

255mm

75mm MAX BAR THICKNESS

50mm DRIP TRAY SPACER

Ø 64mm

Ø 50mm CLEARANCE HOLE REQUIRED Ø

LONGER THOUGH-THE-BAR THREADED TUBE AVAILABLE
SEE DISPENSE SPARES LIST FOR DETAILS



MICRO MATIC
OLYMPUS
INFORMATION SHEET